


COMPATIBLE MATERIAL LIST

V E R S V S
— 3 8 5 —



MICROLAY[®]
3 D P R I N T E R S

May 2022

✓✓ Validated
✓ Validation in process

MICROLAY PrintFit



✓✓ PrintFit Model Golden Brown	Model
✓✓ PrintFit Model Ivory	
✓✓ PrintFit Cast	Cast

DETAX Freeprint

DETAX

✓✓ Model 2.0 385 caramel	
✓✓ Model 2.0 385 grey	
✓✓ Model 2.0 385 light grey	
✓✓ Model 2.0 385 sand	
✓✓ Model 2.0 385 white	Model
✓✓ Model 385 Grey	
✓✓ Model 385 Ivory	
✓✓ Model 385 Sand	
✓✓ Model T 385	
✓✓ Cast 2.0 385	Cast
✓✓ Cast 385	
✓✓ Gingiva 385	Gingiva
✓✓ Temp 385	C&B
✓✓ Denture 385	Denture
✓✓ Ortho 385	SG
✓ Try-in 385	Try-in
✓✓ Tray 2.0 385	Tray
✓✓ Tray 385	
✓✓ IBT 385	IBT

BEGO



✓✓ VarseoWax Model	Model
--------------------	--------------

✓ VarseoWax CAD-Cast	Cast
VarseoSmile Temp	
✓ VarseoSmile Crown Plus	C&B
✓ VarseoSmile Temp	

Keyprint



✓✓ KeyModel	
✓✓ KeyModel Ultra Ivory	
✓✓ KeyModel Ultra Ivory (2022)	Model
✓✓ KeyModel Ultra Light Grey	
✓✓ KeyModel Ultra Light Grey (2022)	
✓✓ KeyOrthoModel	
✓✓ KeyCast	Cast
✓✓ KeyMask	Gingiva
✓✓ KeyGuide	SG
✓ KeyDenture Try-In	Try-in
✓✓ KeyTray	Tray
✓✓ KeyOrtho IBT	IBT

Pro3dure



✓ GR-13 model	Model
✓ GR-13.3 model release	
✓ GR-12 cast	Cast
✓ GR-15 gingiva	Gingiva
✓ GR-17 temporary	
✓ GR-17.1 temporary lt	C&B
✓ GR-14.1 denture	Denture
✓ GR-10 guide	
✓ GR-20 MJF	SG
✓ GR-21 Try In	Try-in
✓ GR-11 tray	Tray
✓ GR-18 IB	IBT
✓ GR-16 Xray	Other

Voco



✓✓ V-Print Model Beige	Model
✓✓ V-Print Model Fast Blue	
✓✓ V-Print Cast Blue	Cast
✓✓ V-Print Dentbase Pink	Denture
✓✓ V-Print SG Clear	SG
✓✓ V-Print Try-In Beige	Try-in
✓✓ V-Print Tray Blue	Tray

Dentona



✓✓ Optiprint Match	
✓✓ Optiprint Model Golden Brown	
✓✓ Optiprint Model Grey	Model
✓✓ Optiprint Model Ivory	
✓✓ Optiprint Ortho-Model	
✓✓ Optiprint Cast	
✓✓ Optiprint Zero	Cast

✓✓ Optiprint Gingiva	Gingiva
✓✓ Optiprint Lumina	C&B
✓✓ Optiprint Temp A2	
✓✓ Optiprint Temp A3	
✓✓ Optiprint Temp B2 385	
✓✓ Optiprint Denture Pink Dark	
✓✓ Optiprint Denture Pink Light	Denture
✓✓ Optiprint Laviva	SG
✓✓ Optiprint Guide 385	
✓✓ Optiprint Mock-up	Try-in
✓✓ Optiprint Tray 385	Tray
✓✓ Optiprint I-B-T	IBT

Dreve



✓ FotoDent Model	Model
✓ FotoDent Model2 385	
✓ FotoDent Setup	
✓✓ FotoDent Biobased Model	
✓ FotoCast 385	Cast
✓ FotoDent Cast	
✓ FotoDent Gingiva 385	Gingiva
✓ FotoDent Denture 385 pink-transparent	Denture
✓ FotoDent Guide 385	SG
✓ FotoDent Tray	Tray
✓ FotoTec DLP.A Beige Opaque1 380	Audiology
✓ FotoTec DLP.A Clear 380	
✓ FotoTec DLP.Flex 70 Shore A	
✓ FotoTec DLP.Flex 90 Shore A	
✓ FotoTec DLP.Flex Clear 380	

Saremco



✓ Crowntec	C&B
------------	-----

NextDent



Model 2.0	Model
Cast	Cast
Gingiva Mask	Gingiva
C&B 3.5	C&B
C&B MFH N1	
C&B MFH N1.5	
Ortho Rigid	SG
SG	
Try-In	Try-in
Ortho IBT	IBT

BASF












✓✓ Ultracur3D DM 2505	Model
-----------------------	-------

GT-Medical



✓✓ Model A2	Model
✓✓ Model Topo	

✓✓ Encias falsas		Gingiva
3Delta		
Model 320 Model Ortho Model Silbergrau		Model
Cast M Cast P		Cast
3DM Admat		
✓✓ Dent Brown		Model
ArmaResin		
✓✓ Model HP ✓✓ Model ST		Model
✓✓ Cast		Cast
✓✓ Temp		C&B
✓✓ Surgical Guide		SG
Asiga		
DentaBase		Denture
SuperWAX		Other
BlueCast		
X-One		Other
DH-Print		
Model Beige		Model
Cast Red		Cast
Provisional C&B A3		C&B
Denture Base		Denture
Tray Pink 405		Tray
Funtodo		
Castable Blend Dentifix		Model
GC		
✓✓ Temp Print Light ✓✓ Temp Print Medium		C&B
Graphy		
Tera Harz TC-80DPA2		C&B
Tera Harz TE-151 Tera Harz TE-160		Other
Harz		

Dental Clear Dental Clear Yellow Dental Model Black Dental Peach Dental Pink Dental Sand	Model
---	--------------

Junction3D



SolusArt Grey SolusArt Grey v3.0	Other
-------------------------------------	--------------

Kulzer



Dima Print Stone Beige	Model
Dima Print Denture Teeth A2	C&B

LiqCreate



Dental Model Pro Grey Premium Model	Model
Castable	Cast
Deep Blue Strong-X Wax Castable	Other

Loctite



<ul style="list-style-type: none"> ✓ 3818 High Accuracy Black ✓ 3820 Ultra Clear ✓ 3843 HDT60 High Toughness Matte Black ✓ 5015 A80 Elastomeric Black ✓ IND147 HDT230 High Heat 	Other
--	--------------

Nyte3D



✓✓ Model Grey	Model
✓✓ Model Sand	
✓✓ Gingiva	Gingiva

PowerResins



✓✓ Dental Model	Model
✓✓ Dental Cast Burn	Cast
✓✓ Temp Light	C&B
✓✓ Denture	Denture
✓✓ SG	SG

Raydent



C&B	C&B
-----	----------------

Shera










SHERAprint-tray	Tray
-----------------	-------------

SolidScapeDL



--	--

DiamondCast		Other
SpotA		
Model		Model
Model Beige		
Cast		Cast
R-Impact		Other
Taglus		
✓✓ Model Resin Beige		Model
✓✓ Model Resin Grey		
UVital		
MH-20		Other
Vericom		
Mazic D Temp		C&B
WhipMix		
Verimodel Ivory		Model
VeriModel OS GoldenBrow		
Verimodel White		
VeriGuide		SG
VeriGuide OS Clear		
VeriTray Neon Green		Tray
DETAX Luxaprint		
✓✓ Cast 2.0		Audiology
✓✓ Cocoon		
✓✓ Flex		
✓✓ Mould blue		
✓✓ Mould clear		
✓✓ Mould fluorescent yellow		
✓✓ Mould intensive blue		
✓✓ Mould light beige		
✓✓ Mould red		
✓✓ Mould rose		
✓✓ Mould rose-orange		
✓✓ Shell beige		
✓✓ Shell black		
✓✓ Shell intensive blue		
✓✓ Shell intensive red		
✓✓ Shell white		
DETAX Medicalprint		

- ✓✓ Mould brilliant-clear 2.0
- ✓✓ Mould clear
- ✓✓ Mould rose
- ✓✓ Mould rose 2.0
- ✓✓ Mould rose-orange
- ✓✓ Shell beige
- ✓✓ Shell beige 2.0
- ✓✓ Shell black
- ✓✓ Shell blue opaque
- ✓✓ Shell red opaque
- ✓✓ Shell skin 2.0
- ✓✓ Shell white

Audiology

Egger



- ✓✓ e3D.C01 Orange
- ✓✓ e3D.M01 Blue
- ✓✓ e3D.M01 Blue Plus
- ✓✓ e3D.M01 Light Brown
- ✓✓ e3D.M01 Neon-yellow
- ✓✓ e3D.M01 Pink-transparent
- ✓✓ e3D.M01 Red
- ✓✓ e3D.M01 Transparent
- ✓✓ e3D.S01 Beige
- ✓✓ e3D.S01 Black
- ✓✓ e3D.S01 Blue
- ✓✓ e3D.S01 Red
- ✓✓ e3D.S01 White

Audiology

Mack4D



- ✓✓ Audio Mold 385nm
- ✓✓ Easy Rip

Audiology

Flexcera

Smile A1

Gingiva

Base Original Pink

Splint